Reduce Equipment Inventory

With Wide Range Conductivity Sensors



Highly Stable Digital Signal

Intelligent Sensor Management (ISM®) technology converts the conductivity measurement into a highly stable, robust digital signal which is sent to the transmitter, enabling the sensor to quickly respond to minor changes in conductivity.




Fast and Easy Installation

ISM's Plug and Measure feature makes sensor installation fast and easy, since all relevant status and configuration information is stored in the sensor and automatically transferred from the sensor to the transmitter during startup.



Easy Traceability

Identification, calibration and maintenance data is stored in the UniCond sensor, which allows for clear traceability. The sensor meets strict NIST-traceable calibration requirements.



Wide Range for Streamlined System Design

Measure makeup, RO, DI and wastewater with a single wide range conductivity sensor. Streamline equipment inventory and system design complexity by reducing the number of fitting types, housings and insertion lengths required.



UniCond Sensors

Superior Measurement Accuracy

The UniCond® conductivity sensor provides an exceptionally wide measurement range due to its advanced built-in circuit. The sensor can be used to measure everything from ultrapure water to brackish water (up to 50,000 µS/cm).

The digital UniCond sensor reduces equipment inventory by enabling the measurement of an extensive water purity range with a single sensor model. The advanced measuring techniques of the UniCond conductivity sensor contribute to superior accuracy over an extended range. UniCond exceeds performance of conventional sensors due to built-in measuring circuits and analog-to-digital signal conversion in the sensor head.

To achieve superior conductivity measurement accuracy, visit:

www.mt.com/UniCond



UniCond Technical Data

UniCond Sensor

Accuracy	0.01 cm-1 sensor: ± 1 % 0.1 cm-1 sensors: ± 1 % for 0.01-5,000 μS/cm;					
	$\pm 3\% > 5,000 \mu S/cm$					
	4-E sensors: ± 4 %					
Repeatability	± 0.25%; ± 2% for 4-E sensors					
Temperature sensor	Pt1000 RTD, IEC 60751, Class A, with NIST-traceable calibration					
Temperature accuracy	± 0.1 °C at 25 °C; ± 0.5 °C for 4-E sensors					
Maximum cable length	91 m (300 ft)					
Finish (sanitary 0.1 cm ⁻¹ sensors)	Ra 0.2 micrometers (8 microinches), 316 L SS is electropolished					
Insulator material	PEEK except for the CPVC sensors					
Response time	90 % of value in < 5s					
Connector	IP 65, mates with 5808027X series cable					

Ordering Information

Description							Order Number
Fitting	Insertion Length	Fitting/Body	Range	Cell Const.	Electrode	Max Pressure at Temp	
	"X" mm (inch)	material	(µS/cm)*	(cm ⁻¹)	Material	bar(g) (psig) at °C (°F)	
34" NPTM	34 (1.35)	PTFE/SS	0.01 - 50,000	0.1	Titanium	17 (250) at 93 (200)	58031404
34" NPTM	132 (5.19)	PTFE/SS	0.01 - 50,000	0.1	Titanium	17 (250) at 93 (200)	58031409
34" NPTM	34 (1.35)	PTFE/SS	0.01 - 50,000	0.1	Monel™	17 (250) at 93 (200)	58031407
34" NPTM	132 (5.19)	PTFE/SS	0.01 - 50,000	0.1	Monel	17 (250) at 93 (200)	58031408
1/2" NPTM	29 (1.14)	PTFE/SS	0.01 - 50,000	0.1	Titanium	17 (250) at 93 (200)	58031406
34" NPT	60 (2.38)	PTFE/SS	0.001 - 500	0.01	Titanium	17 (250) at 93 (200)	58031410
1 ½" Tri-Clamp™	86 (3.38)	Titanium	0.01 - 50,000	0.1	Titanium		58031413 [†]
1 ½" Tri-Clamp	55 (2.17)	316L SS	0.01 – 3,000	0.1	316L SS	14 (203) at 130 (266) & 31 (450) at 25 (77)	58031412 [†]
1 ½" Tri-Clamp	86 (3.38)	316LSS	0.01 - 3,000	0.1	316L SS		58031414†
2" Tri-Clamp	105 (4.13)	316L SS	0.01 – 3,000	0.1	316L SS		58031415 [†]
1" NPTM	28 (1.1)	PEEK	10-1,000,000	4-E	Hastelloy™	7 (100) at 93 (200)	58031421
						14 (200) at 25 (77)	
1" NPTM	28 (1.1)	CPVC	10-1,000,000	4-E	316L SS	3.5 (50) at 80 (176)	58031422
1" NPTM	28 (1.1)	CPVC	10-1,000,000	4-E	Hastelloy	7 (100) at 25 (77)	58031423
1½" Tri-Clamp	25 (1.0)	PEEK	10-1,000,000	4-E	316L SS	- 4.8 (70) at 140 (284) — - 14 (200) at 50 (122) —	58031424†
2" Tri-Clamp	25 (1.0)	PEEK	10-1,000,000	4-E	316L SS		58031425 [†]
1½" Tri-Clamp	25 (1.0)	PEEK	10-1,000,000	4-E	Hastelloy		58031426 [†]

^{*} Megohm-cm = $1/\mu$ S/cm

www.mt.com/pro __

For more information

METTLER TOLEDO Group

Process Analytics Division Local contact: www.mt.com/pro-MOs

Subject to technical changes @06/2021 METTLER TOLEDO. All rights reserved PA2074en Rev B 06/21



Quality certificate.

Development, production and testing to ISO 9001.



CE Compliant



UL listed Meets Canadian Standards

[†] FDA compliant materials with certification to meet EN10204 3.1 & USP <88 > Class VI UniCond and ISM are registered trademarks of the METTLER TOLEDO Group.

All other trademarks are the property of their respective owners.