

Recommended Services for the 5000TOCi

Optimize Uptime and Performance



Maximize Uptime

Expert system services and periodic replacement of critical system components maximizes system availability and productivity. Execution of recommended and scheduled maintenance delivers accurate system measurement with recommended calibration intervals.



Confidence in Compliance

TOC measurements in regulated water systems are necessary for maintaining compliance to pharmacopeia regulations. Expert services by METTLER TOLEDO ensure compliance through periodic calibrations and systems suitability verification of your critical measurement.



Recommended 5000TOCi Services

Frequency	Service Product	Why get it?
At installation	Comprehensive Qualification Installation qualification (IQ) and operational qualification (OQ) using factory calibration data combined with a system suitability test (SST). Includes SST reference solutions. Available within EQPac.	Quick installation and qualification with expert setup
First two years at point of purchase	ExtendedCare Ensure peace of mind and maximize uptime with this full coverage over the first 24 months of your equipment's life. With preventive maintenance right from the start, you minimize possible long term impacts on your equipment too.	Recommended 6-month services inclusive of: <ul style="list-style-type: none"> • Standard full preventive maintenance • Calibration of TOC, conductivity, flow rate, and temperature • Replacement UV lamp and filter • Visual inspection • Required calibration solutions • Spare part and labor replacements for all non-consumable components
After first two years	ComprehensiveCare Continue maximized uptime beyond your systems first 24 months with this comprehensive service offering. Avoid risk and protect your equipment against downtime, performance issues and unexpected repair labor and material cost.	
Every 6 months	System Suitability Test (for compendial water systems) Provides evidence that system performance and analysis meets compliance requirements for Pharmaceutical customers. Includes SST Reference Solutions.	Ensure TOC system meets regulations

5000TOCi Ordering Information

Service Description	Order Number
Comprehensive qualification	B39920003
Extended Care	B39950001
Comprehensive Care	B39910001
Standard Care	B39910002
Basic Care	B39910003
System suitability test	S39905157

Consumables	Order Number
Replacement UV lamp (recommended every 4,500 hours of operation)	58 079 513
System suitability standards	58 091 526
Calibration standards	58 091 529
Combined calibration and SST standards	58 091 537
Calibration standards for extended range calibration	58 091 568
Combined calibration and SST solutions for extended range calibration	58 091 569
Fuse, 1.25A, sensor PCB (For use on both 110 VAC and 220 VAC models)	58 091 519
Filter element, high capacity (Pkg. 2)	58 091 551

Spare Parts	Order Number
Validation support package, 5000TOCi	58 091 570
Pump module	58 091 565
Pipe mounting kit, 1-1/2" (3.8cm) pipe	58 091 521
Filter assembly, high capacity	58 091 550
High pressure regulator	58 091 552
Stainless steel outlet tube	58 091 553
Patch cord, 1 ft (0.3m)	58 080 270
Patch cord, 5 ft (1.5m)	58 080 271
Patch cord, 10 ft (3.0m)	58 080 272
Patch cord, 15 ft (4.5m)	58 080 273
Patch cord, 25 ft (7.6m)	58 080 274
Patch cord, 50 ft (15.2m)	58 080 275
Patch cord, 100 ft (30.5m)	58 080 276
Patch cord, 150 ft (45.7m)	58 080 277
Patch cord, 200 ft (61.0m)	58 080 278
Patch cord, 300 ft (91.4m)	58 080 279

www.mt.com/pro-service

For more information

METTLER TOLEDO Group

Process Analytics Division

Local contact: www.mt.com/pro-MOs

Subject to technical changes

©07/2019 METTLER TOLEDO. All rights reserved

PA2016en Rev A 07/19